



# Power Protection Products, GFCI Receptacles, Self Test, IG, Tamper and Weather Resistant, Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R

By Bryant  
Catalog # [GFST83RIG](#)



Power Protection Products, GFCI Receptacles, Self Test, IG, Tamper and Weather Resistant, Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Red

## Features

- Self Test
- IG
- Tamper and Weather Resistant
- Hospital Grade
- 20A 125V

## General

Catalog Number	GFST83RIG
Color	Red
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Tamper-Resistant, Weather Resistant
Type	Heavy Duty
UPC	781786150560

## Electrical Ratings

Amperage Rating	20 A
-----------------	------

Current / Amperage Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
-----------------	--------

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY B-8 Catalog Page](#)  
[Catalog Page - BRY C-5 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - CIRCUITPRO® Self Test GFCI](#)  
[Specifications - GFST83RIG](#)