



Power Protection Devices, Receptacle, Self Test, GFCI, Commercial Grade, 15A 125V, 2- Pole 3-Wire Grounding, 5- 15R, Brown

By Bryant
Catalog # [GFTRST15](#)

Power Protection Devices, Receptacle, Self Test, GFCI,
Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R,
Brown



Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

General

Color	<ul style="list-style-type: none">• Brown• Marron
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Standard
Type	<ul style="list-style-type: none">• Tamper-Resistant• Tamper-Resistant
UPC	883778122286

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK K-4 Catalog Page](#)
[Catalog Page - WDK Z-8 Catalog Page](#)
[Catalogs - Wiring Device-Kellems Full Catalog](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - CIRCUITPRO® Self Test GFCI](#)
[Literature - 2015 UL GFCI Requirements](#)
[Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
[Sales Drawings - WDK_GFTRST15_DRAWINGS_PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-GFTRST15-SPEC-EN | REV 7/2023