



Power Protection Products, Receptacles, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3- Wire Grounding, 5- 15R, With Nightlight, Almond

By Bryant
Catalog # [GFTRST15ALNL](#)



Power Protection Products, Receptacles, GFCI, Commercial
Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, With
Nightlight, Almond

Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

General

Catalog Number	GFTRST15ALNL
Color	Almond
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass
Style	Nightlight
Type	Tamper-Resistant
UPC	883778123368

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - CIRCUITPRO® Self Test GFCI](#)
- [Sales Drawings - WDK_GFTRST15ALNL_DRAWINGS_PDF](#)
- [Specifications - GFTRST15ALNL](#)