



Power Protection Products, Receptacles, GFCI, Commercial Grade, Self Test, 15A 125V, 2-Pole 3- Wire Grounding, 5- 15R, With Nightlight, Ivory



By Bryant
Catalog # [GFTRST15INL](#)

Power Protection Products, Receptacles, GFCI, Commercial
Grade, Self Test, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, With
Nightlight, Ivory

General

Catalog Number	GFTRST15INL
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none"> • Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Nightlight
Type	Tamper-Resistant
UPC	883778123399

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A

Voltage Rating Description 125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalog Page - WDK K-4 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Literature - CIRCUITPRO® Self Test GFCI](#)
- [Literature - Residential Catalog](#)
- [Sales Drawings - WDK_GFTRST15INL_DRAWINGS_PDF](#)
- [Specifications - GFTRST15INL](#)