



Power Protection Devices, Receptacle, Self Test, GFCI, Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5- 20R, Almond

By Bryant
Catalog # [GFTRST20AL](#)



Power Protection Devices, Receptacle, Self Test, GFCI,
Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R,
Almond

Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

General

Catalog Number	GFTRST20AL
Color	Almond
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass
Style	Standard
Type	Tamper-Resistant
UPC	883778122323

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - CIRCUITPRO® Self Test GFCI](#)
- [Sales Drawings - WDK_GFTRST20AL_DRAWINGS_PDF](#)
- [Specifications - GFTRST20AL](#)