



# Power Protection Products, GFCI Receptacle, Self Test, Commercial Grade, Tamper Resistant, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, With Alarm, Gray

By Bryant  
Catalog # [GFTRST20GYB](#)



Power Protection Products, GFCI Receptacle, Self Test, Commercial Grade, Tamper Resistant, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, With Alarm, Gray

## Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Alarm version provides audible notification of a trip condition

## General

Catalog Number	GFTRST20GYB
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Alarm
Type	Tamper-Resistant
UPC	883778228261

## Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalog Page - WDK K-4 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - CIRCUITPRO® Self Test GFCI Specifications - GFTRST20GYB](#)