



Straight Blade Devices, Receptacle, GFCI, Tamper Resistant, Commercial Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory, 3 Pack

By Bryant
Catalog # [GFTRST2013](#)



Straight Blade Devices, Receptacle, GFCI, Tamper Resistant, Commercial Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory, 3 Pack

Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

General

Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Standard, 3-Pack
Type	Tamper-Resistant
UPC	883778124020

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	3
-----------------	---

Product Assets

[Catalog Page - WDK K-4 Catalog Page](#)
[Catalogs - Wiring Device-Kellems Full Catalog](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-GFTRST2013-SPEC-EN | REV 7/2023