



Power Protection Devices, Receptacle, Self Test, GFCI, IG, TRWR, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Ivory

By Bryant
Catalog # [GFTWRST15IIG](#)



Power Protection Devices, Receptacle, Self Test, GFCI, IG,
TRWR, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding,
5-15R, Ivory

Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Color	<ul style="list-style-type: none"> • Ivory • Ivoire
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Isolated Ground
Type	<ul style="list-style-type: none"> • Tamper-Resistant, Weather Resistant • Tamper-Resistant, Weather Resistant
UPC	883778122750

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalog Page - WDK K-7 Catalog Page](#)
- [Catalogs - Wiring Device-Kellems Full Catalog](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - CIRCUITPRO® Self Test GFCI](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Sales Drawings - WDK_GFTWRST15IIG_DRAWINGS_PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-GFTWRST15IIG-SPEC-EN | REV 7/2023