



**Power Protection Devices,  
Receptacle, Self Test, GFCI, IG,  
TRWR, Commercial Grade, 20A  
125V, 2-Pole 3-Wire Grounding, 5-  
20R, Black**



By Bryant  
Catalog # [GFTWRST20BKIG](#)

Power Protection Devices, Receptacle, Self Test, GFCI, IG, TRWR,  
Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,  
Black

**General**

Catalog Number	GFTWRST20BKIG
Color	Black
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none"> <li>• Base - Nylon</li> <li>• Face - Nylon</li> <li>• Ground Contacts - Brass</li> <li>• Mounting Screws - Zinc plated steel</li> <li>• Mounting Strap - Zinc plated steel</li> <li>• Power Contacts - Brass</li> </ul>
Style	Isolated Ground
Type	Tamper-Resistant, Weather Resistant
UPC	883778122811

**Electrical Ratings**

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating Description	125 V

**Certifications And Compliance**

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

**Logistics**

Carton Quantity	10
-----------------	----

**Product Assets**

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalog Page - WDK K-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - CIRCUITPRO® Self Test GFCI](#)
- [Sales Drawings - WDK\\_GFTWRST20BKIG\\_DRAWINGS\\_PDF](#)
- [Specifications - GFTWRST20BKIG](#)