



Power Protection Devices, Receptacle, Self Test, GFCI, IG, TRWR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Brown

By Bryant
Catalog # [GFTWRST20IG](#)

Power Protection Devices, Receptacle, Self Test, GFCI, IG,
TRWR, Commercial Grade, 20A 125V, 2-Pole 3-Wire
Grounding, 5-20R, Brown



Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Color	<ul style="list-style-type: none">• Brown• Brun
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Isolated Ground
Type	<ul style="list-style-type: none">• Tamper-Resistant, Weather Resistant• Tamper-Resistant, Weather Resistant
UPC	883778122842

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalog Page - WDK K-7 Catalog Page](#)
- [Catalogs - Wiring Device-Kellems Full Catalog](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - CIRCUITPRO® Self Test GFCI](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Sales Drawings - WDK_GFTWRST20IG_DRAWINGS_PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-GFTWRST20IG-SPEC-EN | REV 7/2023