



**Power Protection Devices,
Receptacle, Self Test, GFCI, IG,
TRWR, Commercial Grade, 20A
125V, 2-Pole 3-Wire Grounding, 5-
20R, Ivory**

By Bryant
Catalog # [GFTWRST20IIG](#)



Power Protection Devices, Receptacle, Self Test, GFCI, IG, TRWR,
Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,
Ivory

General

Catalog Number	GFTWRST20IIG
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none"> • Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Isolated Ground
Type	Tamper-Resistant, Weather Resistant
UPC	883778122835

Electrical Ratings

Amperage Rating	20 A
-----------------	------

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalog Page - WDK K-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Literature - CIRCUITPRO® Self Test GFCI](#)
- [Sales Drawings - WDK_GFTWRST20IIG_DRAWINGS_PDF](#)
- [Specifications - GFTWRST20IIG](#)

