



Power Protection Devices, Receptacle, Self Test, GFCI, WR, Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Almond

By Bryant
Catalog # [GFWRST20AL](#)



Power Protection Devices, Receptacle, Self Test, GFCI, WR,
Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,
Almond

Features

- Patented AUTOGUARD® self test technology
- Meets NEC requirements for weather resistance (406.9), UV and corrosion resistance for harsh and damp applications
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Catalog Number	GFWRST20AL
Color	Almond
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass
Style	Standard

Type	Weather Resistant
UPC	883778122484

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Literature - 2015 UL GFCI Requirements](#)
- [Sales Drawings - WDK_GFWRST20_DRAWING_PDF](#)
- [Specifications - GFWRST20AL](#)