



Power Protection Devices,
Receptacle, Self Test, GFCI, WR,
Commercial Grade, 20A 125V, 2-
Pole 3-Wire Grounding, 5-20R,
Gray

By Bryant
Catalog # [GFWRST20GY](#)

Power Protection Devices, Receptacle, Self Test, GFCI, WR,
Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,
Gray

Features

- Patented AUTOGUARD® self test technology
- Meets NEC requirements for weather resistance (406.9), UV and corrosion resistance for harsh and damp applications
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Color	<ul style="list-style-type: none">• Gray• Gris
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Standard
Type	<ul style="list-style-type: none">• Weather Resistant• Weather Resistant
UPC	883778122507



Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK K-8 Catalog Page](#)
[Catalogs - Wiring Device-Kellems Full Catalog](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - 2015 UL GFCI Requirements](#)
[Sales Drawings - WDK_GFWRST20_DRAWING_PDF](#)



A proud member of the Hubbell Family.