



Single Pole Products, Double Female Coupler, 150 Amp Series, White

By Bryant
Catalog # [HBL15DFW](#)



Single Pole Products, Double Female Coupler, 150 Amp Series, White

Application

Temporary Electrical Power

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Double Female Coupler
Material	Brass and Non-Metallic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	1-Pole
Series	Series 15
Style	Female-Female
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Gender Reversing
UPC	783585458700

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	150 A
Connectivity	Plug-In
Current / Amperage Rating	150 A
Current Rating	150 A
Voltage Rating Description	600V AC/DC

Conductor Related

Number Of Conductors	1 Conductor
----------------------	-------------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">National Electric Code (NEC), ANSI/NFPA 70UL and cUL ListedUL Enclosure Types 3R, 4X, 12
----------------------	--

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - Bryant L-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HBL15DFW-SPEC-EN | REV 7/2023