



# Single Pole Products, Double Male Coupler, 150 Amp Series, White

By Bryant  
Catalog # [HBL15DMW](#)



Single Pole Products, Double Male Coupler, 150 Amp Series, White

## General

Application	Temporary Electrical Power
Catalog Number	HBL15DMW
Color	White
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Double Male Coupler
Material	Brass and Non-Metallic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	1-Pole
Series	Series 15
Style	Male-Male
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Gender Reversing Devices
UPC	783585458687

## Dimensions

Display Size	Standard
--------------	----------

## Electrical Ratings

Amperage Rating	150 A
Connectivity	Plug-In
Current / Amperage Rating	150 A
Current Rating	150 A
Voltage Rating Description	600V AC/DC

## Conductor Related

Number of Conductors	1 Conductor
----------------------	-------------

## Certifications And Compliance

Industry Standard(s)	National Electric Code (NEC), ANSI/NFPA 70  UL and cUL Listed  UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	25
-----------------	----

## Product Assets

- [Catalog Page - WDK H-4 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Single Pole Devices](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRY-HBL15DMW-SPEC-EN | REV 6/2024