

Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, Black

By Bryant
Catalog # [HBL15FRBK](#)



Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, Black

Features

- Double Set Screw Termination
- 150 Amp Series
- Black

Application

Extra Heavy Duty Industrial

Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

General

Catalog Number	HBL15FRBK
Color	Blue
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Female Receptacle
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Series	Series 15
Specifications	<ul style="list-style-type: none"> • Base Compound - Thermoplastic Elastomer (TPE) • Contact Material - Brass • Mounting Hole - 3x Ø .20" • Retaining Screw Material - Nylon • Termination - (2) 5/32 Socket Head Set Screws
Style	Double Set Screw Female

Type	Receptacle
UPC	783585458175

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	150 A
Connectivity	Double Set Screw
Current / Amperage Rating	150 A
Current Rating	150 A
Phase	Single Phase
Voltage Rating Description	600V AC/DC
Wattage	90000

Conductor Related

Number Of Wires	None
Wire Size	#4 AWG Type SC/PPC Wire

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • National Electric Code (NEC), ANSI/NFPA 70 • UL and cUL Listed • UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

Logistics

Carton Quantity	25
Pallet Quantity	4500

Product Assets

- [Catalog Page - WDK H-3 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBL15FRBK](#)