



Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, Green

By Bryant
Catalog # [HBL15FRGN](#)



Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, Green

General

Application	Extra Heavy Duty Industrial
Catalog Number	HBL15FRGN
Color	Green
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Female Receptacle
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Performance	Electrical - Amperage Rating - 150A Maximum Electrical - Voltage Ratings - 600V AC Maximum 250V DC Maximum Mechanical - Product Identification - Ratings are a permanent part of device Mechanical - Terminal Accommodation - #8 to #2 AWG
Series	Series 15
Style	Double Set Screw Female
Type	Receptacle
UPC	783585458212

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	150 A
Connectivity	Double Set Screw
Current / Amperage Rating	150 A
Current Rating	150 A
Phase	Single Phase
Voltage Rating Description	600V AC/DC
Wattage	90000

Conductor Related

Number Of Wires	None
Wire Size	#4 AWG Type SC/PPC Wire

Certifications And Compliance

Industry Standard(s)	National Electric Code (NEC), ANSI/NFPA 70 UL and cUL Listed UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

Logistics

Carton Quantity	25
Pallet Quantity	4500

Product Assets

- [Catalog Page - WDK H-3 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Single Pole Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-HBL15FRGN-SPEC-EN | REV 6/2024