



Single Pole Products, Male Plug, 150 Amp Series, Red

By Bryant
Catalog # [HBL15MR](#)



Single Pole Products, Male Plug, 150 Amp Series, Red

Features

- Insulgrip® Style Housing for Superior Gripping
- Non-Conductive Retaining Screw locks contacts in place
- Large Raised Alignment Arrow aids in the mating of devices

Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

General

Catalog Number	HBL15MR
Color	Red
EU RoHS Indicator	Contact Manufacturer
Series	Series 15
Specifications	<ul style="list-style-type: none"> • Base Compound - Thermoplastic Elastomer (TPE) • Contact Material - Brass • Retaining Screw Material - Nylon
Style	Double Set Screw Male

Type	Receptacle
UPC	783585458342

Electrical Ratings

Amperage Rating	150 A
Current / Amperage Rating	150 A
Voltage Rating Description	600V AC/DC

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • National Electric Code (NEC), ANSI/NFPA 70 • UL and cUL Listed • UL Enclosure Types 3R, 4X, 12
----------------------	--

Logistics

Carton Quantity	25
Pallet Quantity	4500

Product Assets

- [Catalog Page - WDK H-3 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBL15MR](#)