



Single Pole Products, Male Inlet, Double Set Screw Termination, 150 Amp Series, Green

By Bryant
Catalog # [HBL15MRGN](#)

Single Pole Products, Male Inlet, Double Set Screw
Termination, 150 Amp Series, Green



Application

Extra Heavy Duty Industrial

General

Color	Green
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Male Inlet
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Performance	<ul style="list-style-type: none">• Electrical - Amperage Rating - 150A Maximum• Electrical - Voltage Ratings - 600V AC Maximum• 250V DC Maximum• Mechanical - Product Identification - Ratings are a permanent part of device• Mechanical - Terminal Accommodation - #8 to #2 AWG
Series	Series 15
Style	Double Set Screw Male
Type	Receptacle
UPC	783585458168

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	150 A
Connectivity	Double Set Screw
Current / Amperage Rating	150 A
Current Rating	150 A
Phase	Single Phase
Voltage Rating Description	600V AC/DC
Wattage	90000

Conductor Related

Number Of Wires	None
Wire Size	#4 AWG Type SC/PPC Wire

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• National Electric Code (NEC), ANSI/NFPA 70• UL and cUL Listed• UL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - Bryant L-3 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HBL15MRGN-SPEC-EN | REV 7/2023