



## Single Pole Products, Paralleling Tee, 150 Amp Series, Green

By Bryant  
Catalog # [HBL15PTGN](#)



Single Pole Products, Paralleling Tee, 150 Amp Series, Green

### Application

Temporary Electrical Power

### General

Color	Green
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Paralleling Tee
Material	Brass and Non-Metallic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	1-Pole
Series	Series 15
Style	Paralleling Tee Femal-Male-Male
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Tee
UPC	783585458595

### Dimensions

Display Size	Standard
--------------	----------

### Electrical Ratings

Amperage Rating	150 A
Connectivity	Plug-In
Current / Amperage Rating	150 A
Current Rating	150 A
Voltage Rating Description	600V AC/DC

### Conductor Related

Number Of Conductors	1 Conductor
----------------------	-------------

### Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>National Electric Code (NEC), ANSI/NFPA 70</li><li>UL and cUL Listed</li><li>UL Enclosure Types 3R, 4X, 12</li></ul>
Nema Rating	Non-NEMA

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Catalog Page - Bryant L-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-HBL15PTGN-SPEC-EN | REV 7/2023