



Single Pole Products, Tapping Tee, 150 Amp Series, Red

By Bryant
Catalog # HBL15TR



Single Pole Products, Tapping Tee, 150 Amp Series, Red

Application

Temporary Electrical Power

General

Catalog Number	HBL15TR
Color	Red
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Tapping Tee
Material	Brass and Non-Metallic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	1-Pole
Series	Series 15
Style	Tapping Tee Female-Female-Male
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Tees and 3-Fers
UPC	783585458656

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	150 A
Connectivity	Plug-In
Current / Amperage Rating	150 A
Current Rating	150 A
Voltage Rating Description	600V AC/DC

Conductor Related

Number of Conductors	1 Conductor
----------------------	-------------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">National Electric Code (NEC), ANSI/NFPA 70UL and cUL ListedUL Enclosure Types 3R, 4X, 12
Nema Rating	Non-NEMA

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - WDK H-4 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Single Pole Devices](#)