



Metal Raceway, 5' Base/Cover, HBL2000 Series, Ivory

By Bryant
Catalog # [HBL2000BCAIV](#)



Metal Raceway, 5' Base/Cover, HBL2000 Series, Ivory

Features

- Higher capacity power applications
- Available in cover only or base and cover options
- Cover is 0.040 Inch (1.016) thick which allows up to 600V AC

Performance

Electrical - Rating - 600V Rated

General

Catalog Number	HBL2000BCAIV
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	NEMA 1 Rating
Item Type	HBL2000 Series
Material	Steel
Series	HBL2000A
Specifications	<ul style="list-style-type: none">• Channel Area (sq. in.) - 0.89• Cover Thickness - 0.040 in. (1.016)• Material - Galvanized Steel
Style	Single Channel

Type	Base and Cover
UPC	783585214030

Dimensions

Length	5 ft
--------	------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Standard C22.2 no. 62• E253976 /E253830 /E253833• UL Standard UL 5
----------------------	--

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - WDK S-48 Catalog Page](#)
[Catalog Page - WDK S-10 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2000BCAIV](#)