




Metal Raceway, 5' Cover, HBL2000 Series, Gray

By Bryant
Catalog # [HBL2000CGY](#)



Metal Raceway, 5' Cover, HBL2000 Series, Gray

Features

- Higher capacity power applications
- Available in cover only or base and cover options
- Cover is 0.040 Inch (1.016) thick which allows up to 600V AC

Performance

Electrical - Rating - 300V Rated

General

Catalog Number	HBL2000CGY
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	NEMA 1 Rating
Item Type	HBL2000 Series
Material	Steel
Series	HBL2000
Specifications	<ul style="list-style-type: none">• Channel Area (sq. in.) - 0.89• Cover Thickness - 0.025 in. (0.635)• Material - Galvanized Steel
Style	Single Channel

Type	Cover Only
UPC	783585214085

Dimensions

Length	5 ft
--------	------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Standard C22.2 no. 62• E253976 /E253830 /E253833• UL Standard UL 5
----------------------	--

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog Page - WDK S-48 Catalog Page](#)
- [Catalog Page - WDK S-10 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - HBL2000CGY](#)