



# Metal PlugTrak, 15A 1 Circuit, 6 Receptacle, 3' Length, Ivory

By Bryant  
Catalog # [HBL20GB306IV](#)



Metal PlugTrak, 15A 1 Circuit, 6 Receptacle, 3' Length, Ivory

## Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

## General

Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number Of Receptacles	6
Performance	<ul style="list-style-type: none"><li>• Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R</li><li>• Mechanical - Wire - #12 AWG Stranded Copper</li></ul>
Type	Single Circuit
UPC	783585214542

## Dimensions

Length	3 ft
--------	------

## Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

## Conductor Related

Wire Size	#12 AWG THHN
-----------	--------------

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Standard C22.2 no. 62</li><li>• E253976 /E253830 /E253833</li><li>• UL Standard UL 5</li></ul>
----------------------	--

## Logistics

Carton Quantity	2
-----------------	---

## Product Assets

[Catalog Page - Bryant P-10 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-HBL20GB306IV-SPEC-EN | REV 7/2023