



# Metal PlugTrak, 15A 1 Circuit, 5 Receptacle, 5' Length, Ivory



By Bryant  
Catalog # [HBL20GB512IV](#)

Metal PlugTrak, 15A 1 Circuit, 5 Receptacle, 5' Length, Ivory

## Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

## Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

## General

Catalog Number	HBL20GB512IV
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	5
Series	Metal
Specifications	<ul style="list-style-type: none"> <li>• Number of Receptacles - 5 Singles</li> <li>• PlugTrak Amperage - 15A</li> <li>• PlugTrak Length - 5 Foot</li> <li>• Receptacle Face - Thermoplastic</li> <li>• Spacing - 12 Inch OC</li> <li>• Wiring Type - Hard Wired</li> </ul>
Style	Standard
Type	Single Circuit

UPC 783585214580

## Dimensions

Length 5 ft

## Electrical Ratings

Current / Amperage Rating 15 A

## Conductor Related

Wire Size #12 AWG THHN

## Certifications And Compliance

- Industry Standard(s)
- CSA Standard C22.2 no. 62
  - E253976 /E253830 /E253833
  - UL Standard UL 5

## Logistics

Carton Quantity 2

## Product Assets

- [Catalog Page - WDK S-51 Catalog Page](#)
- [Catalog Page - WDK S-12 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - HBL20GB512IV](#)