



PLUGTRAK TAMPER RESIST 15A 5FT STEEL IV



By Bryant
Catalog # [HBL20GB512IVTR](#)

PLUGTRAK TAMPER RESIST 15A 5FT STEEL IV

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	HBL20GB512IVTR
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	5
Series	Metal
Specifications	<ul style="list-style-type: none">• Number of Receptacles - 5 Singles• PlugTrak Amperage - 15A• PlugTrak Length - 5 Foot• Receptacle Face - Thermoplastic• Spacing - 12 Inch OC• Wiring Type - Hard Wired

Style	Tamper Resistant
Type	Single Circuit
UPC	783585455914

Dimensions

Length	5 ft
--------	------

Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

Conductor Related

Wire Size	#12 AWG THHN
-----------	--------------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Standard C22.2 no. 62• E253976 /E253830 /E253833• UL Standard UL 5
----------------------	--

Product Assets

- [Catalog Page - WDK S-12 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - HBL20GB512IVTR](#)