



Metal PlugTrak, 15A 1 Circuit, 10 Receptacle, 6' Length, Ivory



By Bryant
Catalog # [HBL20GB606IV](#)

Metal PlugTrak, 15A 1 Circuit, 10 Receptacle, 6' Length, Ivory

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	HBL20GB606IV
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	12
Series	Metal
Specifications	<ul style="list-style-type: none">• Number of Receptacles - 12 Singles• PlugTrak Amperage - 15A• PlugTrak Length - 6 Foot• Receptacle Face - Thermoplastic• Spacing - 6 Inch OC• Wiring Type - Hard Wired
Style	Standard
Type	Single Circuit

UPC 783585214610

Dimensions

Length 6 ft

Electrical Ratings

Current / Amperage Rating 15 A

Conductor Related

Wire Size #12 AWG THHN

Certifications And Compliance

Industry Standard(s)

- CSA Standard C22.2 no. 62
- E253976 /E253830 /E253833
- UL Standard UL 5

Logistics

Carton Quantity 2

Product Assets

[Catalog Page - WDK S-51 Catalog Page](#)
[Catalog Page - WDK S-12 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - HBL20GB606IV](#)