



Metal PlugTrak, 15A 1 Circuit, 8 Receptacle, 6' Length, Gray

By Bryant
Catalog # [HBL20GB609GY](#)



Metal PlugTrak, 15A 1 Circuit, 8 Receptacle, 6' Length, Gray

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

General

Color	<ul style="list-style-type: none">• Gray• Gray
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number Of Receptacles	8
Performance	<ul style="list-style-type: none">• Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R• Mechanical - Wire - #12 AWG Stranded Copper
Type	<ul style="list-style-type: none">• Single Circuit• Single Circuit
UPC	783585214627

Dimensions

Length 6 ft

Electrical Ratings

Current / Amperage Rating 15 A

Conductor Related

Wire Size #12 AWG THHN

Certifications and Compliance

Industry Standard(s)

- CSA Standard C22.2 no. 62
- E253976 /E253830 /E253833
- UL Standard UL 5

Logistics

Carton Quantity 2

Product Assets

[Catalog Page - Bryant P-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.