



Metal PlugTrak, 15A 1 Circuit, 6 Receptacle, 6' Length, Gray

By Bryant
Catalog # [HBL20GB612GY](#)



Metal PlugTrak, 15A 1 Circuit, 6 Receptacle, 6' Length, Gray

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

General

Color	Gray
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number Of Receptacles	6
Performance	<ul style="list-style-type: none">• Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R• Mechanical - Wire - #12 AWG Stranded Copper
Type	Single Circuit
UPC	783585214641

Dimensions

Length	6 ft
--------	------

Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

Conductor Related

Wire Size	#12 AWG THHN
-----------	--------------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Standard C22.2 no. 62• E253976 /E253830 /E253833• UL Standard UL 5
----------------------	--------------------------------------------------------------------------------------------------------------------------------------------

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalog Page - Bryant P-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HBL20GB612GY-SPEC-EN | REV 7/2023