



Metal PlugTrak, 15A 2 Circuit, 5 Receptacle, 5' Length, Ivory

By Bryant
Catalog # [HBL20GBA512IV](#)



Metal PlugTrak, 15A 2 Circuit, 5 Receptacle, 5' Length, Ivory

General

Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number Of Receptacles	5
Performance	<ul style="list-style-type: none">Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20RMechanical - Wire - #12 AWG Stranded Copper

Type	Two Circuits
UPC	783585214719

Dimensions

Length	5 ft
--------	------

Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

Conductor Related

Wire Size	#12 AWG THHN
-----------	--------------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">CSA Standard C22.2 no. 62E253976 /E253830 /E253833UL Standard UL 5
----------------------	--

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalog Page - Bryant P-10 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.