



# Metal PlugTrak, 15A 2 Circuit, 8 Receptacle, 5' Length, Gray



By Bryant  
Catalog # [HBL20GBA609GY](#)

Metal PlugTrak, 15A 2 Circuit, 8 Receptacle, 5' Length, Gray

## Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

## Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

## General

Catalog Number	HBL20GBA609GY
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	8
Series	Metal
Specifications	<ul style="list-style-type: none"><li>• Number of Receptacles - 8 Singles</li><li>• PlugTrak Amperage - 15A</li><li>• PlugTrak Length - 6 Foot</li><li>• Receptacle Face - Thermoplastic</li><li>• Spacing - 9 Inch OC</li><li>• Wiring Type - Hard Wired</li></ul>
Style	Standard
Type	Two Circuits

UPC 783585214726

## Dimensions

Length 6 ft

## Electrical Ratings

Current / Amperage Rating 15 A

## Conductor Related

Wire Size #12 AWG THHN

## Certifications And Compliance

Industry Standard(s)

- CSA Standard C22.2 no. 62
- E253976 /E253830 /E253833
- UL Standard UL 5

## Logistics

Carton Quantity 2

## Product Assets

[Catalog Page - WDK S-51 Catalog Page](#)  
[Catalog Page - WDK S-12 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - HBL20GBA609GY](#)