



# Metal PlugTrak, 15A 2 Circuit, 6 Receptacle, 6' Length, Gray

By Bryant  
Catalog # [HBL20GBA612GY](#)



Metal PlugTrak, 15A 2 Circuit, 6 Receptacle, 6' Length, Gray

## Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

## General

Color	<ul style="list-style-type: none"><li>• Gray</li><li>• Gray</li></ul>
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number Of Receptacles	6
Performance	<ul style="list-style-type: none"><li>• Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R</li><li>• Mechanical - Wire - #12 AWG Stranded Copper</li></ul>
Type	<ul style="list-style-type: none"><li>• Two Circuits</li><li>• Two Circuits</li></ul>
UPC	783585214740

## Dimensions

Length 6 ft

## Electrical Ratings

Current / Amperage Rating 15 A

## Conductor Related

Wire Size #12 AWG THHN

## Certifications and Compliance

Industry Standard(s)

- CSA Standard C22.2 no. 62
- E253976 /E253830 /E253833
- UL Standard UL 5

## Logistics

Carton Quantity 2

## Product Assets

[Catalog Page - Bryant P-10 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.