



# Metal PlugTrak, 15A 2 Circuit, 4 Receptacle, 6' Length, Ivory

By Bryant  
Catalog # [HBL20GBA618IV](#)

Metal PlugTrak, 15A 2 Circuit, 4 Receptacle, 6' Length, Ivory

## Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

## Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

## General

Catalog Number	HBL20GBA618IV
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	4
Series	Metal
Specifications	<ul style="list-style-type: none"> <li>• Number of Receptacles - 4 Singles</li> <li>• PlugTrak Amperage - 15A</li> <li>• PlugTrak Length - 6 Foot</li> <li>• Receptacle Face - Thermoplastic</li> <li>• Spacing - 18 Inch OC</li> <li>• Wiring Type - Hard Wired</li> </ul>
Style	Standard
Type	Two Circuits

UPC 783585214771

## Dimensions

Length 6 ft

## Electrical Ratings

Current / Amperage Rating 15 A

## Conductor Related

Wire Size #12 AWG THHN

## Certifications And Compliance

- |                      |  |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none"> <li>• CSA Standard C22.2 no. 62</li> <li>• E253976 /E253830 /E253833</li> <li>• UL Standard UL 5</li> </ul> |
|----------------------|--|

## Logistics

Carton Quantity 2

## Product Assets

- [Catalog Page - WDK S-51 Catalog Page](#)
- [Catalog Page - WDK S-12 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - HBL20GBA618IV](#)