



Metal PlugTrak, Isolated Ground, 15A 1 Circuit, 5 Receptacle, 6' Length, Gray



By Bryant
Catalog # [HBL20IG606GY](#)

Metal PlugTrak, Isolated Ground, 15A 1 Circuit , 5 Receptacle, 6' Length, Gray

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	HBL20IG606GY
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	12
Series	Metal
Specifications	<ul style="list-style-type: none"> • Number of Receptacles - 12 Singles • PlugTrak Amperage - 15A • PlugTrak Length - 6 Foot • Receptacle Face - Thermoplastic • Spacing - 6 Inch OC • Wiring Type - Hard Wired
Style	Isolated Ground
Type	Single Circuit

UPC 783585214825

Dimensions

Length 6 ft

Electrical Ratings

Current / Amperage Rating 15 A

Conductor Related

Wire Size #12 AWG THHN

Certifications And Compliance

- | | |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none"> • CSA Standard C22.2 no. 62 • E253976 /E253830 /E253833 • UL Standard UL 5 |
|----------------------|--|

Logistics

Carton Quantity 2

Product Assets

- [Catalog Page - WDK S-51 Catalog Page](#)
- [Catalog Page - WDK S-12 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - HBL20IG606GY](#)