



Metal PlugTrak, 20A 125V, 1 Circuit, 6 Receptacle, 3' Length, Gray

By Bryant
Catalog # [HBL24GB306GY](#)

Metal PlugTrak, 20A 125V, 1 Circuit, 6 Receptacle, 3' Length, Gray



Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	HBL24GB306GY
Color	<ul style="list-style-type: none">• Gray•
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	6
Series	Metal
Style	Standard
Type	Single Circuit
UPC	783585214849

Dimensions

Length	3 ft
--------	------

Electrical Ratings

Current / Amperage Rating 20 A

Conductor Related

Wire Size #12 AWG THHN

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Standard C22.2 no. 62• E253976 /E253830 /E253833• UL Standard UL 5
----------------------	--

Logistics

Carton Quantity 2

Product Assets

- [Catalog Page - WDK S-51 Catalog Page](#)
- [Catalog Page - WDK S-12 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand