



Metal PlugTrak, 20A 125V, 1 Circuit, 6 Receptacle, 3' Length, Ivory



By Bryant
Catalog # [HBL24GB306IV](#)

Metal PlugTrak, 20A 125V, 1 Circuit, 6 Receptacle, 3' Length, Ivory

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	HBL24GB306IV
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	6
Series	Metal
Specifications	<ul style="list-style-type: none"> • Number of Receptacles - 6 Singles • PlugTrak Amperage - 20A • PlugTrak Length - 3 Foot • Receptacle Face - Thermoplastic • Spacing - 6 Inch OC • Wiring Type - Hard Wired
Style	Standard
Type	Single Circuit

UPC 783585214856

Dimensions

Length 3 ft

Electrical Ratings

Current / Amperage Rating 20 A

Conductor Related

Wire Size #12 AWG THHN

Certifications And Compliance

- Industry Standard(s)
- CSA Standard C22.2 no. 62
 - E253976 /E253830 /E253833
 - UL Standard UL 5

Logistics

Carton Quantity 2

Product Assets

- [Catalog Page - WDK S-51 Catalog Page](#)
- [Catalog Page - WDK S-12 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - HBL24GB306IV](#)