



PLUGTRAK TAMPER RESIST 20A 5FT STEEL GRY

By Bryant
Catalog # [HBL24GB512GYTR](#)

PLUGTRAK TAMPER RESIST 20A 5FT STEEL GRY

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	HBL24GB512GYTR
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	5
Series	Metal
Specifications	<ul style="list-style-type: none">• Number of Receptacles - 5 Singles• PlugTrak Amperage - 20A• PlugTrak Length - 5 Foot• Receptacle Face - Thermoplastic• Spacing - 12 Inch OC• Wiring Type - Hard Wired
Style	Tamper Resistant
Type	Single Circuit

UPC 783585453088

Dimensions

Length 5 ft

Electrical Ratings

Current / Amperage Rating 20 A

Conductor Related

Wire Size #12 AWG THHN

Certifications And Compliance

Industry Standard(s)

- CSA Standard C22.2 no. 62
- E253976 /E253830 /E253833
- UL Standard UL 5

Logistics

Carton Quantity 2

Product Assets

[Catalog Page - WDK S-12 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - HBL24GB512GYTR](#)