



# Metal PlugTrak, 20A 125V, 1 Circuit, 5 Receptacle, 5' Length, Ivory

By Bryant  
Catalog # [HBL24GB512IV](#)

Metal PlugTrak, 20A 125V, 1 Circuit, 5 Receptacle, 5' Length, Ivory



## Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

## Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

## General

Catalog Number	HBL24GB512IV
Color	<ul style="list-style-type: none"><li>• Ivory</li><li>• </li></ul>
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	5
Series	Metal
Style	Standard
Type	Single Circuit
UPC	783585214894

## Dimensions

Length	5 ft
--------	------

## Electrical Ratings

Current / Amperage Rating 20 A

## Conductor Related

Wire Size #12 AWG THHN

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Standard C22.2 no. 62</li><li>• E253976 /E253830 /E253833</li><li>• UL Standard UL 5</li></ul>
----------------------	--

## Logistics

Carton Quantity 2

## Product Assets

- [Catalog Page - WDK S-51 Catalog Page](#)
- [Catalog Page - WDK S-12 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)