



Metal PlugTrak, 20A 125V, 2 Circuit, 6 Receptacle, 6' Length, Gray

By Bryant
Catalog # [HBL24GBA612GY](#)



Metal PlugTrak, 20A 125V, 2 Circuit, 6 Receptacle, 6' Length, Gray

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

General

Catalog Number	HBL24GBA612GY
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	6
Performance	Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R Mechanical - Wire - #12 AWG Stranded Copper
Series	Metal
Style	Standard
Type	Two Circuits
UPC	783585214986

Dimensions

Length	6 ft
--------	------

Electrical Ratings

Current / Amperage Rating	20 A
---------------------------	------

Conductor Related

Wire Size	#12 AWG THHN
-----------	--------------

Certifications And Compliance

Industry Standard(s)	CSA Standard C22.2 no. 62 E253976 /E253830 /E253833 UL Standard UL 5
----------------------	--

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [Catalog Page - WDK S-51 Catalog Page](#)
- [Catalog Page - WDK S-12 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-HBL24GBA612GY-SPEC-EN | REV 6/2024