



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female, Plug, 300A 600V AC/DC, Single Conductor, Double Set Screws, Black

By Bryant
Catalog # [HBL300FBK](#)



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female, Plug, 300A 600V AC/DC, Single Conductor, Double Set Screws, Black

Features

- Extra Long non-conductive inner sleeve
- Turn and Lock Symbol aids in the mating of devices
- Easily Identifiable Cable with cut off points for secure fit

General

Color	<ul style="list-style-type: none">• Black• Noir
Performance	<ul style="list-style-type: none">• Electrical - Amperage Rating - 400A Maximum• Electrical - Voltage Ratings - 600V AC Maximum• 250V DC Maximum• Environmental - Flammability - HB per UL94 or CSA 22.2. 0.17• Mechanical - Product Identification - Ratings are a permanent part of device• Mechanical - Terminal Accommodation - #6 to 2/O AWG
Series	Series 16
Style	Female
Type	<ul style="list-style-type: none">• Plugs• Plugs
UPC	783585112008

Electrical Ratings

Amperage Rating	300 A
Current / Amperage Rating	300 A
Voltage Rating Description	600V AC/DC

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• National Electric Code (NEC), ANSI/NFPA 70• UL and cUL Listed• UL Enclosure Types 3R, 4X, 12
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant L-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HBL300FBK-SPEC-EN | REV 7/2023