



Heavy Duty Products, Single Pole Devices, Industrial Grade, Male, Plug, 300A 600V AC/DC, Single Conductor, Double Set Screws, Blue



By Bryant
Catalog # [HBL300MBL](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Male, Plug, 300A 600V AC/DC, Single Conductor, Double Set Screws, Blue

Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Environmental - Flammability - HB per UL94 or CSA 22.2. 0.17
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #6 to 2/0 AWG

General

Catalog Number	HBL300MBL
Color	Blue
EU RoHS Indicator	Yes
Series	Series 16
Specifications	<ul style="list-style-type: none">• Base Compound - Thermoplastic Elastomer• Contact Material - Brass• Retaining Screw Material - Nylon
Style	Male
Type	Plugs
UPC	783585112091

Electrical Ratings

Amperage Rating	300 A
Current / Amperage Rating	300 A
Voltage Rating Description	600V AC/DC

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• National Electric Code (NEC), ANSI/NFPA 70• UL and cUL Listed• UL Enclosure Types 3R, 4X, 12
----------------------	--

Logistics

Carton Quantity	50
Pallet Quantity	2500

Product Assets

- [Catalog Page - WDK H-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBL300MBL](#)