



# Heavy Duty Products, Single Pole Devices, Industrial Grade, Male, Plug, 300A 600V AC/DC, Single Conductor, Double Set Screws, Yellow



By Bryant  
Catalog # [HBL300MY](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Male, Plug, 300A 600V AC/DC, Single Conductor, Double Set Screws, Yellow

## Features

- Insulgrip® Style Housing for Superior Gripping
- Non-Conductive Retaining Screw locks contacts in place
- Large Raised Alignment Arrow aids in the mating of devices

## General

Catalog Number	HBL300MY
Color	Yellow
EU RoHS Indicator	Yes
Performance	Electrical - Amperage Rating - 400A Maximum
	Electrical - Voltage Ratings - 600V AC Maximum
	250V DC Maximum
	Environmental - Flammability - HB per UL94 or CSA 22.2. 0.17
	Mechanical - Product Identification - Ratings are a permanent part of device
	Mechanical - Terminal Accommodation - #6 to 2/0 AWG
Series	Series 16
Style	Male
Type	Plugs
UPC	783585112152

## Electrical Ratings

Amperage Rating	300 A
Current / Amperage Rating	300 A
Voltage Rating Description	600V AC/DC

## Certifications And Compliance

Industry Standard(s)	National Electric Code (NEC), ANSI/NFPA 70
	UL and cUL Listed
	UL Enclosure Types 3R, 4X, 12

## Logistics

Carton Quantity	50
Pallet Quantity	2500

## Product Assets

- [Catalog Page - WDK H-6 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Single Pole Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-HBL300MY-SPEC-EN | REV 6/2024