

Heavy Duty Products, Single Pole Devices, Industrial Grade, Female, Plug, 400A 600V AC/DC, Single Conductor, Double Set Screws, Yellow



By Bryant
Catalog # [HBL400FY](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Female, Plug, 400A 600V AC/DC, Single Conductor, Double Set Screws, Yellow

Features

- Extra Long non-conductive inner sleeve
- Turn and Lock Symbol aids in the mating of devices
- Easily Identifiable Cable with cut off points for secure fit

Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Environmental - Flammability - HB per UL94 or CSA 22.2. 0.17
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - 2/0 to 4/0 AWG

General

Catalog Number	HBL400FY
Color	Yellow
EU RoHS Indicator	Yes
Series	Series 16
Specifications	<ul style="list-style-type: none"> • Base Compound - Thermoplastic Elastomer • Contact Material - Brass • Retaining Screw Material - Nylon
Style	Female

Type	Plugs
UPC	783585112251

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Voltage Rating Description	600V AC/DC

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • National Electric Code (NEC), ANSI/NFPA 70 • UL and cUL Listed • UL Enclosure Types 3R, 4X, 12
----------------------	--

Logistics

Carton Quantity	50
Pallet Quantity	2500

Product Assets

[Catalog Page - WDK H-6 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Single Pole Devices](#)
[Specifications - HBL400FY](#)