

## Heavy Duty Products, Single Pole Devices, Industrial Grade, Male, Plug, 400A 600V AC/DC, Single Conductor, Double Set Screws, Red

By Bryant  
Catalog # [HBL400MR](#)



Heavy Duty Products, Single Pole Devices, Industrial Grade, Male, Plug, 400A 600V AC/DC, Single Conductor, Double Set Screws, Red

### Features

- Insulgrip® Style Housing for Superior Gripping
- Non-Conductive Retaining Screw locks contacts in place
- Large Raised Alignment Arrow aids in the mating of devices

### Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Environmental - Flammability - HB per UL94 or CSA 22.2. 0.17
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - 2/0 to 4/0 AWG

### General

Catalog Number	HBL400MR
Color	Red
EU RoHS Indicator	Yes
Series	Series 16
Specifications	<ul style="list-style-type: none"><li>• Base Compound - Thermoplastic Elastomer</li><li>• Contact Material - Brass</li><li>• Retaining Screw Material - Nylon</li></ul>
Style	Male

Type	Plugs
UPC	783585112312

### Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Voltage Rating Description	600V AC/DC

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• National Electric Code (NEC), ANSI/NFPA 70</li><li>• UL and cUL Listed</li><li>• UL Enclosure Types 3R, 4X, 12</li></ul>
----------------------	--

### Logistics

Carton Quantity	50
Pallet Quantity	2500

### Product Assets

[Catalog Page - WDK H-6 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - Single Pole Devices](#)  
[Specifications - HBL400MR](#)