



Heavy Duty Products, Single Pole Devices, Industrial Grade, Male to 6) Females, Distribution Block, 400A 600V AC/DC, Single Conductor, Pre-Wired



By Bryant
Catalog # [HBL7DBBN](#)

Heavy Duty Products, Single Pole Devices, Industrial Grade, Male to 6) Females, Distribution Block, 400A 600V AC/DC, Single Conductor, Pre-Wired, Brown

Application

High Ampacity

General

Color	Brown
Insulation	Insulated Body
Item Type	Distribution Block
Material	Brass and Elastomer
Number Of Pins	1) In, 6) Out- Male 6) Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Amperage Rating - 400A Maximum • Electrical - Voltage Ratings - 600V AC Maximum • 250V DC Maximum • Mechanical - Product Identification - Ratings are a permanent part of the device
Series	Series 16
Style	1-Male, 6-Female
Type	Distribution Block
UPC	783585048802

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

Certifications and Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

Product Assets

[Catalog Page - Bryant L-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.