



# Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male-Male, Tri-Tap, 400A 600V AC/DC, Single Conductor, Pre-Wired, Blue

By Bryant  
Catalog # [HBLF3MBL](#)



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male-Male, Tri-Tap, 400A 600V AC/DC, Single Conductor, Pre-Wired, Blue

## General

Application	High Ampacity
Catalog Number	HBLF3MBL
Color	Blue
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	Tri-Taps
Material	Brass and Elastomer
Number Of Pins	1) In, 3) Out- Male-Female-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	Electrical - Amperage Rating - 400A Maximum  Electrical - Voltage Ratings - 600V AC Maximum 250V DC Maximum  Mechanical - Product Identification - Ratings are a permanent part of the device
Series	Series 16
Style	3-Fer Female-Male-Male-Male
Type	Tees and 3-Fers
UPC	783585112411

## Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

## Certifications And Compliance

Industry Standard(s) [UL 498](#) And [UL1691](#)

## Product Assets

- [Catalog Page - WDK H-8 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Single Pole Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-HBLF3MBL-SPEC-EN | REV 6/2024