



Heavy Duty Products, Single Pole Devices, Industrial Grade, Male-Female-Female-Female, Tri-Tap, 300/400A 600V AC/DC, Single Conductor, Pre-Wired

By Bryant
Catalog # [HBLM3FBK](#)



Heavy Duty Single Pole Industrial Grade Male-Female-Female-Female, Tri-Tap, 300/400A 600V AC/DC, Single Conductor, Pre-Wired

Features

- Industrial Grade
- Male-Female-Female-Female
- Tri-Tap

Application

High Ampacity

Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of the device

General

Catalog Number	HBLM3FBK
Color	Black
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	Tri-Taps
Material	Brass and Elastomer
Number Of Pins	1) In, 3) Out- Male-Female-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Series 16
Specifications	<ul style="list-style-type: none"> • Body Material - Thermoplastic Elastomer

- Contact Material - Brass
 - Product Type - T's" and Tri-Taps
 - Tee and Tap Type - Tri-Tap 3-Fer Male-Female-Female-Female
- Style
- Type
- UPC
- Tees and 3-Fers
- 783585112756

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

Certifications And Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK H-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)
- [Specifications - HBLM3FBK](#)