



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male, Paralleling Tee, 300/400A 600V AC/DC, Single Conductor, Pre-Wired, Green

By Bryant
Catalog # HBLPTGN



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male, Paralleling Tee, 300/400A 600V AC/DC, Single Conductor, Pre-Wired, Green

General

Application	High Ampacity
Catalog Number	HBLPTGN
Color	Green
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	T-Fittings
Material	Brass and Elastomer
Number Of Pins	1) In, 2) Out- Male-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	Electrical - Amperage Rating - 400A Maximum Electrical - Voltage Ratings - 600V AC Maximum 250V DC Maximum Mechanical - Product Identification - Ratings are a permanent part of the device
Series	Series 16
Style	Paralleling Tee Femal-Male-Male
Type	Tees and 3-Fers
UPC	783585113135

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

Certifications And Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK H-8 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Single Pole Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-HBLPTGN-SPEC-EN | REV 6/2024