



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male, Paralleling Tee, 300/400A 600V AC/DC, Single Conductor, Pre-Wired

By Bryant
Catalog # HBLPTY



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Male-Male, Paralleling Tee, 300/400A 600V AC/DC, Single Conductor, Pre-Wired, Yellow

Application

High Ampacity

General

Color	Yellow
Insulation	Insulated Body
Item Type	T-Fittings
Material	Brass and Elastomer
Number Of Pins	1) In, 2) Out- Male-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Amperage Rating - 400A Maximum • Electrical - Voltage Ratings - 600V AC Maximum • 250V DC Maximum • Mechanical - Product Identification - Ratings are a permanent part of the device
Series	Series 16
Style	Paralleling Tee Femal-Male-Male
Type	Tees and 3-Fers
UPC	783585113173

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

Certifications and Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

Product Assets

- [Catalog Page - Bryant L-7 Catalog page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.