



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Female-Male, Tapping "Tee", 300/400A 600V AC/DC, Single Conductor, Pre-Wired, Black

By Bryant
Catalog # [HBLTBK](#)



Heavy Duty Products, Single Pole Devices, Industrial Grade, Female-Female-Male, Tapping "Tee", 300/400A 600V AC/DC, Single Conductor, Pre-Wired, Black

Application

High Ampacity

General

Color	<ul style="list-style-type: none">• Black• Noir
Insulation	Insulated Body
Item Type	T-Fittings
Material	Brass and Elastomer
Number Of Pins	1) In, 2) Out- Male-Female-Female
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	<ul style="list-style-type: none">• Electrical - Amperage Rating - 400A Maximum• Electrical - Voltage Ratings - 600V AC Maximum• 250V DC Maximum• Mechanical - Product Identification - Ratings are a permanent part of the device
Series	Series 16
Style	Tapping Tee Female-Female-Male
Type	Tees and 3-Fers
UPC	783585046525

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

Certifications and Compliance

Industry Standard(s)	UL 498 And UL1691
----------------------	-------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant L-7 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Single Pole Devices](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-HBLTBK-SPEC-EN | REV 7/2023